

VRLA-GEL Battery - Medium and Large Series									
Model	Voltage	Capacity	Hour Rate	Dimension LxWxHxTH		Weight		Terminal Type	Polarity
	(V)	(Ah)		mm	inch	Kg	Lbs		
OT100-6(GEL)	6	6	10HR	195*170*204*211	7.68*6.69*8.03*8.31	14.00	30.86	T3	A
OT120-6(GEL)	6	6	10HR	280*128*203*207	11.02*5.04*7.99*8.15	17.20	37.92	T3	B
OT150-6(GEL)	6	6	10HR	260*180*246*253	10.24*7.09*9.69*9.96	24.90	54.90	T3	B
OT180-6(GEL)	6	6	10HR	306*168*222*227	12.05*6.61*8.74*8.94	27.00	59.52	T3	B
OT200-6(GEL)	6	6	10HR	323*177*225*230	12.72*6.97*8.86*9.06	30.00	66.14	T3	B
OT200-6(GEL)	6	6	10HR	323*177*225*248	12.72*6.97*8.86*9.76	30.00	66.14	B6	B
OT65-12(GEL)/B	12	12	20HR	350*167*173*173	13.78*6.57*6.81*6.81	19.20	42.33	T3	D
OT65-12(GEL)	12	12	10HR	350*167*173*173	13.78*6.57*6.81*6.81	20.60	45.42	T3	D
OT75-12(GEL)	12	12	10HR	260*168*212*219	10.24*6.61*8.35*8.62	22.90	50.49	T1	C
OT75-12(GEL)	12	12	10HR	260*168*222*222	10.24*6.61*8.74*8.74	22.90	50.49	B3	C
OT85-12(GEL)	12	12	10HR	260*168*212*219	10.24*6.61*8.35*8.62	25.40	56.00	T1	C
OT85-12(GEL)	12	12	10HR	260*168*222*222	10.24*6.61*8.74*8.74	25.40	56.00	B3	C
OT90-12(GEL)	12	12	10HR	307*169*208*228	12.09*6.65*8.19*8.98	27.00	59.52	B11	C
OT100-12(GEL)/B	12	12	20HR	333*173*216*222	13.11*6.81*8.5*8.74	28.10	61.95	T3	C
OT100-12(GEL)	12	12	10HR	333*173*216*222	13.11*6.81*8.5*8.74	30.50	67.24	T3	C
OT100-12(GEL)/A	12	12	10HR	333*173*216*222	13.11*6.81*8.5*8.74	31.20	68.78	T3	C
OT120-12(GEL)/B	12	12	20HR	406*172*208*237	15.98*6.77*8.19*9.33	34.00	74.96	T2	C
OT120-12(GEL)	12	12	10HR	406*172*208*237	15.98*6.77*8.19*9.33	36.60	80.69	B4	C
OT120-12(GEL)	12	12	10HR	406*172*208*237	15.98*6.77*8.19*9.33	36.60	80.69	T2	C
OT150-12(GEL)	12	12	10HR	484*170*241*241	19.06*6.69*9.49*9.49	42.50	93.70	B5	C
OT150-12(GEL)	12	12	10HR	484*170*241*241	19.06*6.69*9.49*9.49	42.50	93.70	T3	C
OT180-12(GEL)	12	12	10HR	532*209*215*245	20.94*8.23*8.46*9.65	53.40	117.73	B6	E
OT200-12(GEL)	12	12	10HR	522*239*217*222	20.55*9.41*8.54*8.74	60.20	132.72	W	E
OT200-12(GEL)	12	12	10HR	522*239*217*222	20.55*9.41*8.54*8.74	60.20	132.72	T3	E
OT200-12(GEL)	12	12	10HR	522*239*217*242	20.55*9.41*8.54*9.53	60.2	132.72	B6	E
OT220-12(GEL)	12	12	10HR	522*239*217*242	20.55*9.41*8.54*9.53	66.1	145.73	B6	E
OT250-12(GEL)	12	12	10HR	520*269*220*245	20.47*10.59*8.66*9.65	72.3	159.39	B7	E
OT250-12(GEL)	12	12	10HR	520*269*220*225	20.47*10.59*8.66*8.86	72.3	159.39	T2	E
OT250-12(GEL)	12	12	10HR	520*269*220*225	20.47*10.59*8.66*8.86	72.3	159.39	W	E